


## Nista Devices Technical Support: +41 55 5085814 support@nistadevices.com Documentation on all Nista Devices GmbH products can be found on the website - http://www.nistadevices.com/

## Configuration IP39-4x for P2P Call with GIGASET Maxwell 10

- 1. IP39-4x configuration
  - IP39-4x and Maxwell phone shall be connected to the IP network with the IP addresses from the same Network subnet range.
  - Enter to IP39-4x web-management interface
  - Navigate to Telephony / Day and Night Settings and fill Day and Night destinations as shown on the e-mail below



• Alternatively Navigate to Telephony / Day and Night Settings and fill Day and Night destinations as shown on the e-mail below:




Where: in string sip:111@192.168.1.35

- 192.168.1.35 - The Gigaset Maxwell 10 phone IP address




- 111 The Gigaset Maxwell 10 phone extension ( see explanation in further in document)
- 2. Gigaset Maxwell 10 Configuration
  - Enter to Maxwell 10 Settings screen and fill configuration fields as shown on the picture below:



Where Authentication password is: 1234

• Enter to Maxwell 10 Advanced Settings screen and fill configuration fields as shown on the picture below:



Where 192.168.1.50 – The IP39-4x Door phone IP address

2